

# Fiber-optic cable SOOC-TB-M-A5-2-R25

Part number: 552827

FESTO



## Data sheet

Feature	Value
Type code	SOOC
Note on materials	RoHS-compliant
Method of measurement	Through-beam sensor
Minimum object diameter	0.1 mm
Special feature of fibre-optic cable	Series
Working range	250 mm
Ambient temperature	-55 °C ... 70 °C
Head size	Rectangle 10x10x5 mm
Fibre-optic cable length	2 m
Min. bending radius	25 mm
Outside diameter	2.2 mm
Housing material	Brass, nickel-plated
Fiber-optic cable	PE
Degree of protection	IP66
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS conformity	VDMA24364 zone III