

Fiber-optic cable SOOC-TB-P-C5-2-R10

Part number: 552828

FESTO



Data sheet

Feature	Value
Type code	SOOC
Note on materials	RoHS-compliant
Method of measurement	Fork light barrier
Minimum object diameter	0.2 mm
Special feature of fibre-optic cable	Fork light barrier
Working range	5 mm
Ambient temperature	-55 °C ... 70 °C
Head size	Rectangle 41x15x7 mm Fork pit 5x29 mm
Fibre-optic cable length	2 m
Min. bending radius	10 mm
Outside diameter	1.25 mm
Housing material	ABS
Fiber-optic cable	PE
Degree of protection	IP66
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS conformity	VDMA24364 zone III