

# Adapter lens SASF-L1-LS2-M4

Part number: 552831

FESTO



## Data sheet

Feature	Value
Type code	SASF
Corrosion resistance class (CRC)	1 - Low corrosion stress
Degree of protection	IP66
Ambient temperature	-30 °C ... 150 °C
Tightening torque	-0.2 Nm ... 0.6 Nm
Product weight	0.7 g
Lens function	Focusing Light spot diameter 0.7 mm at a distance of 10 mm Depending on fiber-optic cable
Housing material	Aluminum Anodized