


Fine filter
MS9-LFM-N3/4-BUV-DA
Part number: 553100

FESTO



Data sheet

Feature	Value
Series	MS
Size	9
Type code	MS9-LFM
Structural design	Fiber filter
Grade of filtration	1 µm
Condensate drain	Fully automatic Manual, non-detenting
Symbol	00991544
Operating pressure	2 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4]
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:7:3]
Max. standard flow rate for air quality class	7000 l/min
Min. standard flow rate for air quality class	350 l/min
Filter efficiency	99.99 %
Max. condensate volume	225 ml
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Residual oil content	0.5 mg/m ³
Differential pressure display	Visual display
Type of mounting	Optionally: Line installation With accessories
Mounting position	Vertical +/- 5°
Pneumatic connection 1	3/4 NPT
Pneumatic connection 2	3/4 NPT
Housing material	Die-cast aluminum
Covering material	PA
Compressed air filter material	Borosilicate fiber
Material of bowl	Wrought aluminum alloy
Inspection window material	PA
Seals material	NBR
Product weight	2000 g