

Bellows kit DADB-S1-32-S351-375

Part number: 553453

FESTO



Data sheet

Feature	Value
Outside diameter	38 mm
Size	32
Stroke range	351 mm ... 375 mm
Piston rod extension	115 mm
Type code	DADB
Design	Round
Mounting position	Any
Structural design	Bellows kit with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C ... 80 °C
Product weight	92 g
Type of mounting	With threaded pin With internal thread
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Adaption parts material	PA-reinforced
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel