


# Fork light barrier SOOF-M-FL-SM-C30-N

Part number: 553554

FESTO



## Data sheet

Feature	Value
Type code	SOOF
Symbol	00991640
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	Free of copper and PTFE Contains paint-wetting impairment substances RoHS-compliant
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Fork light barrier
Type of light	Red
Minimum object diameter	0.5 mm
Ambient temperature	-10 °C ... 60 °C
Repetition accuracy	0.02 mm
Switching output	NPN
Switching element function	Switchable
Hysteresis	≤0.25 mm
Max. switching frequency	4000 Hz
Max. output current	200 mA
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 35 V
Residual ripple	± 5 %
Idle current	30 mA
Reverse polarity protection	for operating voltage connections
Electrical connection	3-pin M8x1 Plug
Size	Clevis 30x35 mm
Fork gap	30 mm
Product weight	75 g
Housing material	Die-cast zinc Painted
Switching status indication	LED yellow
Setting options	Potentiometer
Degree of protection	IP67
Insulation voltage	50 V

<b>Feature</b>	<b>Value</b>
Surge resistance	0.8 kV
Corrosion resistance class (CRC)	0 - No corrosion stress
Contamination level	3