

Axial kit EAMM-A-K62-140A

Part number: 557993

FESTO



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	47 Nm
Product weight	1590 g
Interface code, actuator	K62
Interface code, motor in	140A
Note on materials	RoHS-compliant