

# Quick coupling EAMD-19-15-10-8X10

Part number: 557998

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	10 mm
Diameter of holder 2	8 mm
Size	19
Nominal length	15 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	10000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.445 kgmm <sup>2</sup>
Transferable torque	2 Nm
Product weight	13 g
Note on materials	RoHS-compliant