

# Drive shaft EAMB-34-6-25X26-23X27

Part number: 558037

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	25 mm
Diameter of holder 2	23 mm
Size	120
Nominal length	26 mm
Type code	EAMB
Mounting position	Any
Max. rotational speed	5500 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	18.2 kgmm <sup>2</sup>
Transferable torque	100 Nm
Product weight	201 g
Note on materials	RoHS-compliant