


# Quick coupling EAMC-42-66-11-12

Part number: 558313

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	11 mm
Diameter of holder 2	12 mm
Size	42
Nominal length	66 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	6000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	45.5 kgmm <sup>2</sup>
Transferable torque	17 Nm
Product weight	166 g
Note on materials	RoHS-compliant