


Quick coupling EAMC-56-58-19-25

Part number: 558315

FESTO



Data sheet

Feature	Value
Diameter of holder 1	19 mm
Diameter of holder 2	25 mm
Size	56
Nominal length	58 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	5500 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	60 Nm
Product weight	275 g
Note on materials	RoHS-compliant