

Push-in fitting NPQM-D-G38-Q10-P10

Part number: 558669

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 8 mm |
| Type code | NPQM-D |
| Type of seal on screwed trunion | Sealing ring |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -20 °C ... 70 °C |
| Nominal tightening torque | 9 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 22.6 g |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 10 mm |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated |
| Material of tubing seal | NBR |