

Push-in connector NPQM-D-Q6-S4-P10

Part number: 558767

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	2.5 mm
Type code	NPQM-D
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 70 °C
Product weight	10 g
Pneumatic connection 1	Push-in sleeve QS-4
Pneumatic connection 2	for pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Material of tubing seal	NBR