

Push-in bulkhead connector NPQM-H-Q8-E-P10

Part number: 558808

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	7 mm
Type code	NPQM-H
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 70 °C
Product weight	39.5 g
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Nut material	Brass, nickel-plated
Material of tubing seal	NBR