

Push-in sleeve NPQM-D-S8-E-P10

Part number: 558813

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	6 mm
Type code	NPQM-D
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 70 °C
Product weight	7.5 g
Pneumatic connection 1	Push-in sleeve QS-8
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated