

# Push-in L-fitting NPQM-LK-G18-Q6-P10

Part number: 558819

FESTO



## Data sheet

| Feature   | Value   |
|---|---|
| Size  | Standard                                      |
| Nominal width                                   | 5 mm  |
| Type code                                       | NPQM-LK                                       |
| Type of seal on screwed trunion                 | Sealing ring                                  |
| Structural design                               | Push-pull principle                           |
| Operating pressure for entire temperature range | -0.95 bar ... 16 bar                          |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media        | Operation with oil lubrication possible       |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                      |
| Ambient temperature                             | -20 °C ... 70 °C                              |
| Nominal tightening torque                       | 6 Nm  |
| Tolerance for nominal tightening torque         | ± 20%   |
| Product weight                                  | 24.4 g  |
| Pneumatic connection 1                          | G1/8  |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 6 mm    |
| Note on materials                               | RoHS-compliant                                |
| Housing material                                | Brass, nickel-plated                          |
| Hollow bolt material                            | Brass, nickel-plated                          |
| Material of tubing seal                         | NBR   |