

# Push-in L-fitting NPQM-LH-G14-Q8-P10

Part number: 558833

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	6.5 mm
Type code	NPQM-LH
Type of seal on screwed trunnion	Sealing ring
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 70 °C
Nominal tightening torque	7.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	49.3 g
Pneumatic connection 1	G1/4
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Hollow bolt material	Brass, nickel-plated
Material of tubing seal	NBR