

Quick coupling EAMC-20-30-6-6

Part number: 558901

FESTO



Data sheet

Feature	Value
Diameter of holder 1	6 mm
Diameter of holder 2	6 mm
Size	20
Nominal length	30 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	9000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	1.06 kgmm ²
Transferable torque	2.3 Nm
Product weight	20 g
Note on materials	RoHS-compliant