

Hood VMPAL-KM-SD25-IP67-0

Part number: 560428

FESTO



Data sheet

Feature	Value
Type code	VMPAL
Product weight	100 g
Electrical connection	Customizable
Approved cable diameter	5 mm ... 13 mm
Connection cross section	0.2 mm ² ... 0.5 mm ²
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-5 °C ... 80 °C
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress