

Electrical manifold module VMPAL-EVAP-10-1

FESTO

Part number: 560961



Data sheet

Feature	Value
Valve size	10 mm
Type code	VMPAL
Max. no. of valve positions	1
Max. no. of solenoid coils	1
Integrated function	Valve function assignment color-coded
Nominal operating voltage DC	24 V
Corrosion resistance class (CRC)	3 - High corrosion stress
Ambient temperature	-5 °C ... 50 °C
Product weight	9 g
Housing colour	Gray
Housing material	PA
Note on materials	RoHS-compliant