

# Distributor FR-4-3/8

Part number: 561602

FESTO



## Data sheet

Feature	Value
Nominal width	16 mm
Type code	FR
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 60 °C
No. of outlets	3
No. of supply lines	1
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Housing material	Wrought aluminum alloy Anodized