

Control block CPX-CM-HPP

Part number: 562214

FESTO



Data sheet

Feature	Value
Type code	CPX
Ambient temperature	-5 °C ... 50 °C
Product weight	140 g
CE marking (see declaration of conformity)	As per EU low voltage directive
Degree of protection	IP65 IP67
Storage temperature	-20 °C ... 70 °C
Note on materials	RoHS-compliant
Power failure buffering	10 ms
Total number of axes	4
Dimensions W x L x H	50 mm x 107 mm x 55 mm
Control interface	CAN bus
Fieldbus interface	1x socket, M9, 5-pin
Device-specific diagnostics	Channel-oriented and module-oriented diagnostics Undervoltage/short circuit of modules Diagnostic memory
Configuration support	MMI handheld terminal
Parameterization	forcing of channels System parameter
Baud rate	1 Mbit/s
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Protocol	FHPP
Intrinsic current consumption at nominal operating voltage	Typ. 80 mA
Max. address capacity outputs	32 byte
Max. address capacity inputs	32 byte
LED display (product-specific)	Error PL: load supply
Housing material	PA-reinforced PC