

Stroke reduction HGRT-HR-20

Part number: 564297

FESTO



Data sheet

Feature	Value
Size	20
Adjustable end position range/length	25 mm
Type code	HGRT-HR
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Type of mounting	Screwed on to pneumatic gripper
Note on materials	RoHS-compliant
Lock nut material	Case-hardened steel
Material of screws	Steel