

# Push-in Y-connector QBY-1/2T-3/8-U

Part number: 564825

FESTO



## Data sheet

| Feature   | Value  |
|---|--|
| Size  | Standard   |
| Nominal width                                   | 7.01 mm  |
| Type code                                       | QBY  |
| Mounting position                               | Any  |
| Structural design                               | Push-pull principle  |
| Operating pressure for entire temperature range | -0.951 bar ... 9.997 bar                                       |
| Temperature-dependent operating pressure        | -0.951 bar ... 9.997 bar                                       |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]                  |
| Information on operating and pilot media        | Operation with oil lubrication possible                        |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                       |
| Ambient temperature                             | 0 °C ... 60 °C   |
| Product weight                                  | 26.195 g   |
| Pneumatic connection 1                          | For pneumatic tubing outside diameter 1/2"                     |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 3/8"                     |
| Releasing ring color                            | Gray   |
| Note on materials                               | Contains paint-wetting impairment substances<br>RoHS-compliant |
| Housing material                                | PBT  |
| Releasing ring material                         | POM  |
| Material of tubing seal                         | NBR  |
| Material of tube retaining claw                 | High-alloy stainless steel                                     |