


# Pressure sensor SDE5-V1-NF-Q6E-V-K

Part number: 567470

FESTO



## Data sheet

Feature	Value
Type code	SDE5
Symbol	00992257
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
KC characters	KC EMC
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Method of measurement	Piezoresistive pressure sensor
Pressure measuring range initial value	0 bar
Pressure measuring range end value	-1 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Repetition accuracy in ± %FS	0.3 %FS
Temperature co-efficient in ± %FS/K	0.05 %FS/K
Analog output	0 - 10 V
Output characteristic curve initial value	0 V
End value output characteristic curve	10 V
Precision analog output in ± %FS	3 %FS
Linearity error in ± % FS	0.3 %FS
Short-circuit protection	yes
DC operating voltage range	15 V ... 30 V
Reverse polarity protection	for all electrical connections
Electrical connection	3-wire Cable as per EN 60947-5-2
Cable length	2.5 m
Type of mounting	With accessories
Mounting position	Any
Pneumatic connection	QS-6
Product weight	47 g
Housing material	PA POM
Ready status indication	LED green

Feature	Value
Degree of protection	IP40
Corrosion resistance class (CRC)	2 - Moderate corrosion stress