

Push-in sleeve QBH-5/16-1/4-U

Part number: 567783

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	3.988 mm
Type code	QBH
Mounting position	Any
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.951 bar ... 9.997 bar
Temperature-dependent operating pressure	-0.951 bar ... 9.997 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	2.013 g
Pneumatic connection 1	Push-in sleeve QS-1/4"
Pneumatic connection 2	Push-in sleeve QS-5/16"
Releasing ring color	Gray
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel