

Plastic tubing PUN-H-5/32-NT-150-CB

Part number: 567962

FESTO



Data sheet

Feature	Value
External-Ø inches	5/32
Bending radius relevant for flow rate	15.85 mm
Min. bending radius	6.096 mm
Type code	PUN-H
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: >5 million cycles as per FN 942021
Temperature-dependent operating pressure	-0.993 bar ... 9.997 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
For use in the food industry	See supplementary material information
Ambient temperature	-35 °C ... 63 °C
Product weight by length	0.09 kg/m
Pneumatic connection	For plug connection outside diameter 5/32"
Color	Natural
Shore hardness	D 52 +/-3
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)