

# Plastic tubing PEN-5/8-BL-150-CB

Part number: 569895

FESTO



## Data sheet

Feature	Value
External-Ø inches	5/8
Bending radius relevant for flow rate	124.968 mm
Min. bending radius	59.741 mm
Type code	PEN
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: >5 million cycles as per FN 942021
Temperature-dependent operating pressure	-0.993 bar ... 9.997 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Ambient temperature	-30 °C ... 60 °C
Product weight by length	1.158 kg/m
Pneumatic connection	For plug connection outside diameter 5/8"
Color	Blue
Shore hardness	D 52 +/-3
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	PE