

End plate VMPAL-EPL-CPX

Part number: 570783

FESTO



Data sheet

Feature	Value
Width	40 mm
Length	107.3 mm
Type code	VMPAL
Max. no. of valve positions	32
Valve manifold design	Valve sizes can be mixed
Max. no. of solenoid coils	32
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Nominal operating voltage DC	24 V
Corrosion resistance class (CRC)	3 - High corrosion stress
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-5 °C ... 50 °C
Product weight	130 g
Electrical connection 1, function	Fieldbus
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	Internally for CPX
Note on materials	RoHS-compliant
End plate material	Die-cast aluminum PA-reinforced