

# Cable socket NEFU-X22F-M12G4

Part number: 572225

FESTO



## Data sheet

Feature	Value
Width	36 mm
Height	40 mm
Length	40 mm
Type code	NEFU
Type of mounting	With through-hole
Product weight	30 g
Fieldbus interface	Socket, M12x1, 4-pin, A-coded
AS-Interface DC operating voltage range	26.5 V ... 31.6 V
Nominal operating voltage DC AS-Interface	26.5 V
Degree of protection	IP65 In mounted state as per IEC 60529
Ambient temperature	-25 °C ... 75 °C
Storage temperature	-25 °C ... 85 °C
Note on materials	RoHS-compliant
Housing material	PA
Cover material	PA