

Barb tubing fitting N-1-P-19

Part number: 572260

FESTO



Data sheet

Feature	Value
Nominal width	16.5 mm
Type code	N
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Pneumatic connection 1	External thread R1
Pneumatic connection 2	For tubing I.D. 19 mm
Note on materials	RoHS-compliant