

# Manifold rail VABM-L1-10G-G18-4-GR

Part number: 573423

FESTO



## Data sheet

Feature	Value
Width dimension	10.5 mm
Type code	VABM
Mounting position	Any
Max. no. of valve positions	4
Certification	c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 60 °C
Product weight	329 g
Pilot air port 12/14	M5
Pilot exhaust air port 82/84	M5
Pneumatic connection 1	G1/8
Pneumatic connection 3	G1/8
Pneumatic connection 5	G1/8
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy