

# Plug NECC-S1G9-C2-M

Part number: 576031

FESTO



## Data sheet

| Feature                                    | Value                               |
|--|-------------------------------------|
| Height                                     | 39.4 mm                             |
| Length                                     | 58 mm                               |
| Type code                                  | NECC                                |
| Product weight                             | 24 g                                |
| Fieldbus interface                         | Sub-D, 9-pin, socket                |
| Electrical connection                      | 9-pin/9-pin<br>Sub-D/screw terminal |
| Baud rate                                  | 1 Mbit/s                            |
| Approved cable diameter                    | 8 mm                                |
| Approved cable diameter                    | 8 mm                                |
| Degree of protection                       | IP40                                |
| Ambient temperature                        | -20 °C ... 70 °C                    |
| CE marking (see declaration of conformity) | As per EU low voltage directive     |
| Note on materials                          | RoHS-compliant                      |
| Corrosion resistance class (CRC)           | 1 - Low corrosion stress            |