


Control block for two-hand start ZSB-1/8-B

Part number: 576656

FESTO



Data sheet

Feature	Value
Nominal width	4 mm
Type code	ZSB
Actuation type	Pneumatic
Mounting position	Any
Symbol	00991790
Safety function	Two-hand control
Performance Level (PL)	Two-hand control/category 1, performance level c
Operating pressure	4 bar ... 8 bar
Standard nominal flow rate	50 l/min
CE marking (see declaration of conformity)	as per EU machinery directive
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Certificate issuing authority	IFA 1201046
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	420 g
Type of mounting	Optionally: With through-hole With internal thread
Pneumatic connection 2	G1/8
Pneumatic connection 3	G1/8
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum
Seals material	NBR
Housing material	Wrought aluminum alloy Anodized