

Blanking plug NPQH-P-S14-P10

Part number: 578262

FESTO



Data sheet

Feature	Value
Size	Standard
Type code	NPQH
Mounting position	Any
Pack size	10
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Certificate issuing authority	NSF C0523185
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See declaration of conformity NSF/ANSI 169
Ambient temperature	0 °C ... 150 °C
Product weight	26.5 g
Pneumatic connection 1	Push-in sleeve QS-14
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated