

# Push-in sleeve NPQH-D-S6-E-P10

Part number: 578318

**FESTO**



## Data sheet

| Feature                                         | Value                                                                                                                                        |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Size                                            | Standard                                                                                                                                     |
| Nominal width                                   | 4 mm                                                                                                                                         |
| Type code                                       | NPQH                                                                                                                                         |
| Mounting position                               | Any                                                                                                                                          |
| Pack size                                       | 10                                                                                                                                           |
| Operating pressure for entire temperature range | -0.95 bar ... 20 bar                                                                                                                         |
| Certificate issuing authority                   | NSF C0523185                                                                                                                                 |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]<br>Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a> |
| Information on operating and pilot media        | Operation with oil lubrication possible                                                                                                      |
| Corrosion resistance class (CRC)                | 3 - High corrosion stress                                                                                                                    |
| For use in the food industry                    | See declaration of conformity<br>NSF/ANSI 169                                                                                                |
| Ambient temperature                             | 0 °C ... 150 °C                                                                                                                              |
| Product weight                                  | 5.1 g                                                                                                                                        |
| Pneumatic connection 1                          | Push-in sleeve QS-6                                                                                                                          |
| Pneumatic connection 2                          | Push-in sleeve QS-6                                                                                                                          |
| Note on materials                               | RoHS-compliant                                                                                                                               |
| Housing material                                | Brass, nickel-plated                                                                                                                         |
| Releasing ring material                         | Brass, nickel-plated                                                                                                                         |