

blanking screw NPQH-BK-G14-P10

Part number: 578407

FESTO



Data sheet

Feature	Value
Size	Standard
Type code	NPQH
Type of seal on screwed trunnion	Sealing ring
Mounting position	Any
Pack size	10
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Certificate issuing authority	NSF C0523185
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See declaration of conformity NSF/ANSI 169
Ambient temperature	0 °C ... 150 °C
Max. tightening torque	15 Nm
Product weight	8.9 g
Pneumatic connection 1	External thread G1/4
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Material of threaded seal	FPM
Releasing ring material	Brass, nickel-plated