

Pneumatic terminal LT-2-PK-3-DA

Part number: 5866

FESTO



Data sheet

Feature	Value
Type code	LT
Operating pressure	0.1 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Ambient temperature	-10 °C ... 60 °C
Product weight	5.2 g
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant