

Elbow quick connector LCK-1/4-PK-4-KU

Part number: 6261

FESTO



Data sheet

Feature	Value
Nominal width	3.4 mm
Type code	LCK
Type of seal on screwed trunnion	Sealing edge
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 16 bar
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	External thread G1/4
Pneumatic connection 2	for barbed fitting, inside diameter 4 mm, with nut
Note on materials	Free of copper and PTFE
Housing material	POM