

Quick connector CK-3/8-PK-6-KU

Part number: 6460

FESTO



Data sheet

Feature	Value
Nominal width	5.3 mm
Type code	CK
Type of seal on screwed trunnion	Sealing edge
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Note on materials	RoHS-compliant
Housing material	POM