


OR gate OS-1/4-B

Part number: 6682

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type code | OS |
| Valve function | OR function |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Type of mounting | With through-hole |
| Standard nominal flow rate | 1170 l/min |
| Operating pressure | 1 bar ... 10 bar |
| Ambient temperature | -10 °C ... 60 °C |
| Housing material | Wrought aluminum alloy |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Nominal width | 6,5 mm |
| Mounting position | Any |
| Symbol | 00991102 |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Temperature of medium | -10 °C ... 60 °C |
| Product weight | 110 g |
| Pneumatic connection 3 | G1/4 |
| Note on materials | RoHS-compliant |
| Seals material | NBR |