

Distributor block FR-4-1/4-C

Part number: 7849

FESTO



Data sheet

Feature	Value
Nominal width	11.5 mm
Type code	FR
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	-10 °C ... 80 °C
Product weight	60 g
No. of outlets	3
No. of supply lines	1
Pneumatic connection 1	Internal thread G1/4
Pneumatic connection 2	Internal thread G1/4
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum