

Connecting cable NEBC-S1G25-K-2.0-N-S1G25

Part number: 8001375

FESTO



Data sheet

Feature	Value
Type code	NEBC
Electrical connection	25-pin Plug, straight Sub-D/Sub-D
Cable length	2 m
Cable diameter	7 mm
Cable design	Shielded
Degree of protection	IP40 In mounted state
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
Color cable sheath	Gray
Housing colour	Gray