

Connecting cable NEBC-S1G25-K-5.0-N-S1G25

Part number: 8001376

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type code | NEBC |
| Electrical connection | 25-pin Plug, straight Sub-D/Sub-D |
| Cable length | 5 m |
| Cable diameter | 7 mm |
| Cable design | Shielded |
| Degree of protection | IP40 In mounted state |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| Note on materials | Contains paint-wetting impairment substances RoHS-compliant |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Color cable sheath | Gray |
| Housing colour | Gray |