

Solenoid coil VACS-C-C1-7

Part number: 8025336

FESTO



Data sheet

Feature	Value
Type code	VACS
Mounting position	Any
Duty cycle	100%
Insulation class	H
Coil characteristics	48 V DC: 2.4 W
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
Product weight	37.1 g
Electrical connection	Form C as per EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper