

# Double nipple NPFC-D-2R18-M

Part number: 8030278

**FESTO**



## Data sheet

| Feature                          | Value                                        |
|----------------------------------|----------------------------------------------|
| Type code                        | NPFC                                         |
| Threaded fitting material        | Brass, nickel-plated                         |
| Pack size                        | 10                                           |
| Operating pressure               | -0.95 bar ... 50 bar                         |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [-:--] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                     |
| Ambient temperature              | -20 °C ... 150 °C                            |
| Product weight                   | 9.4 g                                        |
| Pneumatic connection 1           | R1/8                                         |
| Pneumatic connection 2           | R1/8                                         |
| Note on materials                | RoHS-compliant                               |