

Double nipple NPFC-D-R38-R12-M

Part number: 8030285

FESTO



Data sheet

Feature	Value
Type code	NPFC
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:~:]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 150 °C
Product weight	38.42 g
Pneumatic connection 1	R3/8
Pneumatic connection 2	R1/2
Note on materials	RoHS-compliant