

Sleeve NPFC-S-2M5-F

Part number: 8030290

FESTO



Data sheet

Feature	Value
Type code	NPFC
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 150 °C
Product weight	3.13 g
Pneumatic connection 1	M5
Pneumatic connection 2	M5
Note on materials	RoHS-compliant