

**Sleeve**  
**NPFC-S-2G38-F**  
Part number: 8030293

**FESTO**



**Data sheet**

| Feature                          | Value                                        |
|----------------------------------|----------------------------------------------|
| Type code                        | NPFC                                         |
| Threaded fitting material        | Brass, nickel-plated                         |
| Pack size                        | 10                                           |
| Operating pressure               | -0.95 bar ... 50 bar                         |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [-:~:] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                     |
| Ambient temperature              | -20 °C ... 150 °C                            |
| Product weight                   | 35.7 g                                       |
| Pneumatic connection 1           | G3/8                                         |
| Pneumatic connection 2           | G3/8                                         |
| Note on materials                | RoHS-compliant                               |