

# Extension NPFC-E2-2G18-FM

Part number: 8030302

FESTO



## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Type code                        | NPFC   |
| Threaded fitting material        | Brass, nickel-plated                         |
| Pack size                        | 10   |
| Operating pressure               | -0.95 bar ... 50 bar                         |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                     |
| Ambient temperature              | -20 °C ... 150 °C                            |
| Product weight                   | 21.4 g                                       |
| Pneumatic connection 1           | G1/8   |
| Pneumatic connection 2           | G1/8   |
| Note on materials                | RoHS-compliant                               |